
FANUC ROBOSHOT SI-20A Vertical Injection Unit

FANUC







Vertical Injection Unit

This vertical injection unit can be installed on top of the ROBOSHOT. Two different types of units can be adapted to a machine range of 100 ton to 300 tons. Fitted with FANUC's latest CNC, the unit offers stable, precision moulding and is encased in a space-saving electrical cabinet.

Features and Benefits:

- controlled by FANUC's latest CNC
- same accuracy and repeatability as any other ROBOSHOT
- can be installed on current ROBOSHOT models
- integrated screen on ROBOSHOT operation screen



FANUC ROBOSHOT SI-20A						
Item	Unit	Specification				
Screw diameter	mm	14	16	18	20	22
Screw stroke	mm	56	56	75	75	75
Maximum injection volume	cm ³	9	11	19	24	29
Maximum injection speed	mm/s	300				
Maximum injection pressure	MPa	200	180	140	130	120
Maximum pack pressure	MPa	180	160	120	110	100
Maximum injection rate	cm³/s	46	60	76	94	114
Maximum screw rotation speed	min ⁻¹	250				
Nozzle touch force	kN	3				
Number of heaters	Barrel	3				
	Nozzle	1				
Heater capacity	kW	2.4	2.8	3.1	3.5	3.8
Machine weight (injection unit)	ton	0.65 (approximately)				
Machine weight (control unit)	ton	0.15 (approximately)				

Technical information subject to changes without prior notice. All rights reserved. ©2018 FANUC Europe Corporation