



Multi component moulding

Horizontal Injection Unit

This horizontal injection unit can be fitted to the side of the ROBOSHOT α -SiA models. Optional FANUC servomotors are available to control rotary tables from the ROBOSHOT SI-300HA. It is flexible and easy to integrate into your ROBOSHOT cell.

Features and Benefits

- controlled by FANUC's latest CNC
- same accuracy and repeatability as any other ROBOSHOT
- exchangeable between different ROBOSHOT models
- easy to integrate



FANUC ROBOSHOT SI-300HA						
Item	Unit		Specification			
Screw diameter	mm	26	28	32	36	
Screw stroke	mm	95	95	128	144	
Maximum injection volume	cm ³	50	58	103	147	
Maximum Injection speed	mm/s		330			
Maximum injection pressure	MPa	260	240	220	190	
Maximum pack pressure	MPa	260	220	200	170	
Maximum injection rate	cm³/s	175	203	265	336	
Maximum screw rotation speed	min ⁻¹		450			
Nozzle touch force	kN		15			
Number of pyrometers	Barrel		3			
	Nozzle		1			
Heater capacity	kW	6.5	7.2	8.4	9.1	
Machine weight	ton		1.9			