FANUC





INTEGRATED SERVICES

I/O, 24VDC, solenoid valves and air lines standard on board

Next level accuracy for cleanroom applications

- Rated ISO Class 5 for cleanroom operation
- NSF-H1 food-grade grease and anti-rust bolts for food handling applications
- Equipped of a bellow to protect the spindle during cleaning operation
- Featuring a white epoxy coating and IP54 for protection against contamination from limited amounts of dust and other particles as well as water spray
- Highly suitable for tray food and cleanroom applications that require cleaning procedure
- Ultra-compact footprint and robot design minimise interference with peripheral devices
- Web based user interface (*i*RProgrammer) for intuitive and ease-of use programming via tablet or PC (no *i*Pendant Touch required)
- Integrated services e.g. I/O, 24VDC, solenoid valves and air lines in the arm reduce costs and simplify integration
- Fast cycle time thanks to high speed motion

STRONG ARM 6 kg max payload, 650 mm reach

SR-6iA/C





	Motion range (°) Maximum speed (°/s)						?/s)										
Controlled axes	Repeatability (mm)	Mechanical weight (kg)	J1	J2	73	J4	J5	Ј6	J1	J2	73	J4	J5	J6	J4 Inertia (kgm²)	J5 Inertia (kgm²)	J6 Inertia (kgm²)
4	± 0.01 (J1,J2, J3) ± 0.004 (J4)	32	296	300	210mm	1440	-	-	440	700	2000 mm/sec	2500	-	-	0,12	-	-

Working range
Operating space of J3 axis rotation center R 300 R 650 170 90 With Tool flange option (ISO STANDARD FLANGE)

Ä Robot	SR-6 <i>i</i> A/C
Robot footprint [mm]	180 x 260 (394)
Mounting position Floor	•
Mounting position Ceiling	
Mounting position Angle	
Mounting position Wall	
Controller	R-30iB Plus
Compact Plus	•
Open air cabinet	-
Mate cabinet	-
A-cabinet	-
B-cabinet	_
iPendant Touch	-
Electrical connections	
Voltage 50/60Hz 3phase [V]	-
Voltage 50/60Hz 1phase [V]	200-230
Average power consumption [kW]	0.35
Integrated services	
Integrated signals on upper arm In/Out	4/4
Integrated air supply	2
Integrated solenoid valve	2
Environment	
Acoustic noise level [dB]	<70
Ambient temperature [° C]	0-45
Protection	
Body standard/optional	IP54
Wrist & J3 arm standard/optional	IP54
Cleanroom class (ISO Class 5)	•
Auxiliary	
Max. push-down force (Newton)	200