

α-S150iA Mechanical specifications



Clamping unit						
Clamping mechanism	Double toggle					
Tonnage [kN tonf]	1500 150 (1800 180)					
Maximum and minimum die height Doubleplaten [mm]	500-200 (600-200)					
Maximum and minimum die height Singleplaten [mm]	575-275 (675-275)					
Clamping stroke [mm]	440					
Locating ring diameter [mm]	Ø 160					
Tie bar spacing, HxV [mm]	560 x 510					
Platen size, HxV [mm]	800 x 750					
Minimum mold size, HxV [mm] *1	325 x300					
Ejector stroke [mm]	150					
Maximum ejector force [kN tonf]	35 3.5					
Injection unit						
Screw diameter [mm]	32	36	40	44	48	52
Injection stroke [mm]	150	150	150	176	176	208
Max. injection volume [cm ³]	121	153	188	268	318	442
Nozzle touch force [kN tonf]	30 3.0					
Max. Injection Speed mm/s *3	200					
Max. injection pressure (high-pressure filling mode) [MPa] *2*4	-	-	-	-	-	-
Max. injection pressure [MPa] *2	280	280	260	220	190	160*7
Max. pack pressure [MPa] *2	280	280	220	190	160	130*7
Max. injection rate [cm ³ /s] *3	160	203	251	304	361	424
Max. screw rotation speed [min ⁻¹]	300					
Machine weight Doubleplaten Singleplaten [t] *5	7.05 ≈ 6.8					
Max. Injection Speed mm/s *3	330					
Max. injection pressure (high-pressure filling mode) [MPa] *2*4	380	345	280	-	-	-
Max. injection pressure [MPa] *2	280	280	260	220	190	160
Max. pack pressure [MPa] *2	280	280	260	220	190	160
Max. injection rate [cm ³ /s] *3	265	335	414	501	597	700
Max. screw rotation speed [min ⁻¹]	400					
Machine weight Doubleplaten Singleplaten [t] *5	7.2 ≈ 6.95					
Screw and Barrel						
Number of heater [Barrel]	3					
Number of heater [Nozzle]	1					
Total heater wattage [kW]	12.0	13.0	14.9	15.9	17.9	20.2

● standard - not available () with hardware and/or software option

*1) Smaller mold than this size may limit clamp force.

*2) The maximum injection pressure and maximum pack pressure is not melt pressure but injection unit output.

- The maximum injection pressure and maximum pack pressure is the maximum value can be set.

- The maximum injection pressure and maximum pack pressure might be limited depending on the molding condition.

*3) Maximum injection rate and maximum injection speed is a theoretical value.

- Maximum injection rate and maximum injection speed can not be guaranteed when the injection pressure is maximum.

*4) The maximum injection pressure setting at high pressure filling mode option.

- There is a limitation in injection time setting and pack time setting, when high pressure filling mode option is selected. (Contact sales for detail)

- High pressure resistance barrel and nozzle are necessary, when high pressure filling option is selected. (Contact sales for detail)

*5) The machine without option.

*6) The pressure conversion is 1MPa=10kgf/cm².

*7) The molding condition might be limited by the resin. (Contact sales for detail)

α-S150iA Dimensions

