

M-710iC/70T (Top mount)




Max. load capacity
at wrist: **70 kg**



Max. reach:
1900 mm

Controlled axes	Repeatability (mm)	Mechanical weight (kg)	Motion range [°]						Maximum speed [°/s]						J4 Moment/Inertia (Nm/kgm ²)	J5 Moment/Inertia (Nm/kgm ²)	J6 Moment/Inertia (Nm/kgm ²)
			J1	J2	J3	J4	J5	J6	J1	J2	J3	J4	J5	J6			
6	± 0.07	410	*1	261	491	720	250	720	*1	120	120	225	225	225	294/28	294/28	147/11

Working range



Robot

Robot footprint [mm]

M-710iC/70T
535 X 550

Mounting position Floor

●

Mounting position Upside down

●

Mounting position Angle

●



Controller

Open air cabinet

-

Mate cabinet

○

A-cabinet

●

B-cabinet

○

iPendant Touch

●

Electrical connections

Voltage 50/60Hz 3phase [V]

380-575

Voltage 50/60Hz 1phase [V]

-

Average power consumption [kW]

2.5

Integrated services

Integrated signals on upper arm In/Out

8/8

Integrated air supply

1

Environment

Acoustic noise level [dB]

71.3

Ambient temperature [° C]

0-45

Protection

Body standard/optional

IP54/IP67

Wrist & J3 arm standard/optional

IP67

*1) depending on rail specification

● standard ○ on request - not available

() with hardware and/or software option